

1/25/2024 4:52:10 PM  
F:\Projects\2023\Sanford Consortium for Regenerative Medicine\Drawings\MECHANICAL SCHEDULES.dwg

Warning: It is a violation of the law for any person, unless acting under the direction of a licensed architect, to alter an item in any way. If an item in this document is altered, the altering architect, if other than the architect of record, shall affix the item his seal and the notation "altered by" followed by his signature and the date of such alteration, and the specific description of the alteration.

MECHANICAL SCHEDULES

| REHEAT COILS |                          |                        |      |        |                |                   |                   |            |        |             |      |          |              |              |               |                  |                        |         |    |
|--------------|--------------------------|------------------------|------|--------|----------------|-------------------|-------------------|------------|--------|-------------|------|----------|--------------|--------------|---------------|------------------|------------------------|---------|----|
| UNIT NO.     | MANUFACTURER & MODEL NO. | SERVICE                | CFM  | A.P.D. | ENT. AIR (°F.) | CAPACITY (M.B.H.) | HEATING HOT WATER |            |        |             | ROWS | FINS/IN. | LENGTH (IN.) | HEIGHT (IN.) | CONTROL VALVE | OPER. WT. (LBS.) | BRANCH PIPE SIZE (IN.) | REMARKS |    |
|              |                          |                        |      |        |                |                   | ENT. (°F.)        | LVG. (°F.) | G.P.M. | P. D. (FT.) |      |          |              |              |               |                  |                        |         |    |
| RC B029      | TSI                      | CONFICAL B029          | 340  | 0.2    | 55             | 9.4               | 180               | 150        | 0.7    | 5.0         | 2    | 8        | 12           | 9            | CV 5.1        | 15               | 0.75                   |         |    |
| RC B030      | TSI                      | CONFICAL B030          | 200  | 0.2    | 55             | 5.5               | 180               | 150        | 0.4    | 5.0         | 2    | 8        | 9            | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC B032      | TSI                      | SCOPE B032             | 1050 | 0.2    | 55             | 28.9              | 180               | 150        | 1.9    | 5.0         | 2    | 8        | 18           | 15           | CV 5.2        | 35               | 0.75                   |         | 22 |
| RC 1102      | TSI                      | LAB 1101-1103 INTERIOR | 1675 | 0.2    | 55             | 46.1              | 180               | 150        | 3.1    | 5.0         | 2    | 8        | 24           | 18           | CV 5.2        | 55               | 0.75                   |         |    |
| RC 1105      | TSI                      | LAB 1104-1106 INTERIOR | 1720 | 0.2    | 55             | 47.3              | 180               | 150        | 3.2    | 5.0         | 2    | 8        | 24           | 18           | CV 5.3        | 55               | 0.75                   |         |    |
| RC 1104      | TSI                      | LAB 1101-1106 EXTERIOR | 1680 | 0.2    | 55             | 64.7              | 180               | 150        | 4.4    | 5.0         | 2    | 8        | 24           | 18           | CV 5.4        | 55               | 1                      |         |    |
| RC 1107      | TSI                      | BREAKROOM 1107         | 1150 | 0.2    | 55             | 44.3              | 180               | 150        | 3      | 5.0         | 2    | 8        | 24           | 12           | CV 5.2        | 40               | 0.75                   |         |    |
| RC 1301      | TSI                      | LAB SUPPORT 1301       | 640  | 0.2    | 55             | 24.7              | 180               | 150        | 1.7    | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |    |
| RC 1303      | TSI                      | TISSUE 1303            | 750  | 0.2    | 55             | 20.7              | 180               | 150        | 1.4    | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |    |
| RC 1304      | TSI                      | FUME HOOD 1304         | 200  | 0.2    | 55             | 5.5               | 180               | 150        | 0.4    | 5.0         | 2    | 8        | 9            | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 1305      | TSI                      | TISSUE 1305            | 750  | 0.2    | 55             | 20.7              | 180               | 150        | 1.4    | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |    |
| RC 1109      | TSI                      | LAB 1108-1110 INTERIOR | 1750 | 0.2    | 55             | 48.2              | 180               | 150        | 3.3    | 5.0         | 2    | 8        | 24           | 18           | CV 5.3        | 55               | 0.75                   |         |    |
| RC 1112      | TSI                      | LAB 1111-1113 INTERIOR | 1735 | 0.2    | 55             | 47.8              | 180               | 150        | 3.2    | 5.0         | 2    | 8        | 24           | 18           | CV 5.3        | 55               | 0.75                   |         |    |
| RC 1111      | TSI                      | LAB 1108-1113 EXTERIOR | 1620 | 0.2    | 55             | 44.6              | 180               | 150        | 3      | 5.0         | 2    | 8        | 24           | 18           | CV 5.2        | 55               | 0.75                   |         |    |
| RC 1309      | TSI                      | HISTOLOGY 1309         | 980  | 0.2    | 55             | 37.8              | 180               | 150        | 2.6    | 5.0         | 2    | 8        | 18           | 15           | CV 5.2        | 35               | 0.75                   |         |    |
| RC 1311      | TSI                      | HISTOLOGY 1311         | 475  | 0.2    | 55             | 13.1              | 180               | 150        | 0.9    | 5.0         | 2    | 8        | 12           | 12           | CV 5.1        | 20               | 0.75                   |         |    |
| RC 1313      | TSI                      | DARK ROOM 1313         | 285  | 0.2    | 55             | 7.9               | 180               | 150        | 0.6    | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 1318      | TSI                      | COPY 1318, MAIL 1319   | 180  | 0.2    | 55             | 5                 | 180               | 150        | 0.4    | 5.0         | 2    | 8        | 9            | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 1314      | TSI                      | IT 1314                | 50   | 0.2    | 55             | 1.4               | 180               | 150        | 0.1    | 5.0         | 2    | 8        | 6            | 6            | CV 5.1        | 5                | 0.75                   |         |    |
| RC 1202      | TSI                      | RECEPTION 1202         | 220  | 0.2    | 55             | 6.1               | 180               | 150        | 0.5    | 5.0         | 2    | 8        | 9            | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 1116      | TSI                      | OFFICE 1116            | 130  | 0.2    | 55             | 4.3               | 180               | 150        | 0.3    | 5.0         | 2    | 8        | 6            | 6            | CV 5.1        | 5                | 0.75                   |         |    |
| RC 1115      | TSI                      | ASSISTANT MANAGER 1115 | 125  | 0.2    | 55             | 4.9               | 180               | 150        | 0.4    | 5.0         | 2    | 8        | 6            | 6            | CV 5.1        | 5                | 0.75                   |         |    |
| RC 1114      | TSI                      | BUILDING MANAGER 1114  | 160  | 0.2    | 55             | 6.2               | 180               | 150        | 0.5    | 5.0         | 2    | 8        | 9            | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 1907      | TSI                      | IT 1907                | 370  | 0.2    | 55             | 14.3              | 180               | 150        | 1      | 5.0         | 2    | 8        | 12           | 9            | CV 5.2        | 15               | 0.75                   |         |    |
| RC 1909      | TSI                      | GLASSWASH 1909         | 3600 | 0.2    | 55             | 118.8             | 180               | 150        | 8      | 5.0         | 2    | 8        | 36           | 24           | CV 5.5        | 110              | 1.25                   |         |    |
| RC 1820      | TSI                      | ROOMS 1820, 1819, 1819 | 1200 | 0.2    | 55             | 39.6              | 180               | 150        | 2.7    | 5.0         | 2    | 8        | 24           | 15           | CV 5.2        | 45               | 0.75                   |         |    |
| RC 2102      | TSI                      | LAB 2101-2103 INTERIOR | 1765 | 0.2    | 55             | 48.6              | 180               | 150        | 3.3    | 5.0         | 2    | 8        | 24           | 18           | CV 5.3        | 55               | 0.75                   |         |    |
| RC 2105      | TSI                      | LAB 2104-2106 INTERIOR | 1290 | 0.2    | 55             | 35.5              | 180               | 150        | 2.4    | 5.0         | 2    | 8        | 24           | 15           | CV 5.2        | 45               | 0.75                   |         |    |
| RC 2104      | TSI                      | LAB 2101-2106 EXTERIOR | 1260 | 0.2    | 55             | 34.7              | 180               | 150        | 2.4    | 5.0         | 2    | 8        | 24           | 15           | CV 5.2        | 45               | 0.75                   |         |    |
| RC 2107      | TSI                      | ENTRY 2107             | 660  | 0.2    | 55             | 25.5              | 180               | 150        | 1.7    | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |    |
| RC 2301      | TSI                      | TISSUE 2301            | 930  | 0.2    | 55             | 35.9              | 180               | 150        | 2.4    | 5.0         | 2    | 8        | 15           | 15           | CV 5.2        | 30               | 0.75                   |         |    |
| RC 2303      | TSI                      | TISSUE 2303            | 750  | 0.2    | 55             | 20.7              | 180               | 150        | 1.4    | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |    |
| RC 2304      | TSI                      | FUME HOOD 2304         | 200  | 0.2    | 55             | 5.5               | 180               | 150        | 0.4    | 5.0         | 2    | 8        | 9            | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 2306      | TSI                      | LAB SUPPORT 2306       | 425  | 0.2    | 55             | 11.7              | 180               | 150        | 0.8    | 5.0         | 2    | 8        | 12           | 9            | CV 5.1        | 15               | 0.75                   |         |    |
| RC 2601      | TSI                      | ADMINISTRATION 2601    | 260  | 0.2    | 55             | 7.2               | 180               | 150        | 0.5    | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 2803      | TSI                      | COMPUTATIONAL LAB 2803 | 360  | 0.2    | 55             | 13.9              | 180               | 150        | 1      | 5.0         | 2    | 8        | 12           | 9            | CV 5.2        | 15               | 0.75                   |         |    |
| RC 2804      | TSI                      | CONFERENCE 2804        | 260  | 0.2    | 55             | 10.1              | 180               | 150        | 0.7    | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 2806      | TSI                      | LAB 2805-2807 INTERIOR | 1125 | 0.2    | 55             | 31                | 180               | 150        | 2.1    | 5.0         | 2    | 8        | 24           | 12           | CV 5.2        | 40               | 0.75                   |         |    |
| RC 2809      | TSI                      | LAB 2808-2810 INTERIOR | 1600 | 0.2    | 55             | 44                | 180               | 150        | 3      | 5.0         | 2    | 8        | 24           | 18           | CV 5.2        | 55               | 0.75                   |         |    |
| RC 2808      | TSI                      | LAB 2805-2810 EXTERIOR | 1680 | 0.2    | 55             | 64.7              | 180               | 150        | 4.4    | 5.0         | 2    | 8        | 24           | 18           | CV 5.4        | 55               | 1                      |         |    |
| RC 2605      | TSI                      | TISSUE 2605            | 750  | 0.2    | 55             | 28.9              | 180               | 150        | 2      | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |    |
| RC 2606      | TSI                      | LAB SUPPORT 2606       | 380  | 0.2    | 55             | 10.5              | 180               | 150        | 0.7    | 5.0         | 2    | 8        | 12           | 9            | CV 5.1        | 15               | 0.75                   |         |    |
| RC 2607      | TSI                      | FUME HOOD 2607         | 200  | 0.2    | 55             | 5.5               | 180               | 150        | 0.4    | 5.0         | 2    | 8        | 9            | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 2608      | TSI                      | TISSUE 2608            | 750  | 0.2    | 55             | 20.7              | 180               | 150        | 1.4    | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |    |
| RC 2109      | TSI                      | LAB 2108-2110 INTERIOR | 1735 | 0.2    | 55             | 47.8              | 180               | 150        | 3.2    | 5.0         | 2    | 8        | 24           | 18           | CV 5.3        | 55               | 0.75                   |         |    |
| RC 2112      | TSI                      | LAB 2111-2113 INTERIOR | 1260 | 0.2    | 55             | 34.7              | 180               | 150        | 2.4    | 5.0         | 2    | 8        | 24           | 15           | CV 5.2        | 45               | 0.75                   |         |    |
| RC 2111      | TSI                      | LAB 2108-2113 EXTERIOR | 1260 | 0.2    | 55             | 48.6              | 180               | 150        | 3.3    | 5.0         | 2    | 8        | 24           | 15           | CV 5.3        | 45               | 0.75                   |         |    |
| RC 2308      | TSI                      | TISSUE 2308            | 750  | 0.2    | 55             | 20.7              | 180               | 150        | 1.4    | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |    |
| RC 2310      | TSI                      | LAB SUPPORT 2310       | 475  | 0.2    | 55             | 13.1              | 180               | 150        | 0.9    | 5.0         | 2    | 8        | 12           | 12           | CV 5.1        | 20               | 0.75                   |         |    |
| RC 2311      | TSI                      | FUME HOOD 2311         | 250  | 0.2    | 55             | 6.9               | 180               | 150        | 0.5    | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 2312      | TSI                      | TISSUE 2312            | 750  | 0.2    | 55             | 20.7              | 180               | 150        | 1.4    | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |    |
| RC 2313      | TSI                      | LAB SUPPORT 2313       | 255  | 0.2    | 55             | 7.1               | 180               | 150        | 0.5    | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 2318      | TSI                      | COMPUTATIONAL LAB 2813 | 160  | 0.2    | 55             | 4.4               | 180               | 150        | 0.3    | 5.0         | 2    | 8        | 9            | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 2314      | TSI                      | IT 2314, CORRIDOR 2201 | 290  | 0.2    | 55             | 8                 | 180               | 150        | 0.6    | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 2116      | TSI                      | CONFERENCE 2116        | 525  | 0.2    | 55             | 20.3              | 180               | 150        | 1.4    | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |    |
| RC 2115      | TSI                      | ADMINISTRATION 2115    | 105  | 0.2    | 55             | 3.9               | 180               | 150        | 0.3    | 5.0         | 2    | 8        | 6            | 6            | CV 5.1        | 5                | 0.75                   |         |    |
| RC 2114      | TSI                      | COMPUTATIONAL LAB 2114 | 180  | 0.2    | 55             | 6.2               | 180               | 150        | 0.5    | 5.0         | 2    | 8        | 9            | 8            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 2811      | TSI                      | BREAK 2811             | 1240 | 0.2    | 55             | 47.8              | 180               | 150        | 3.2    | 5.0         | 2    | 8        | 24           | 15           | CV 5.3        | 45               | 0.75                   |         |    |
| RC 2813      | TSI                      | LAB 2812-2814 INTERIOR | 1395 | 0.2    | 55             | 38.4              | 180               | 150        | 2.6    | 5.0         | 2    | 8        | 24           | 15           | CV 5.2        | 45               | 0.75                   |         |    |
| RC 2816      | TSI                      | LAB 2815-2817 INTERIOR | 1660 | 0.2    | 55             | 45.7              | 180               | 150        | 3.1    | 5.0         | 2    | 8        | 24           | 18           | CV 5.2        | 55               | 0.75                   |         |    |
| RC 90        | TSI                      | LAB 2812-2817 EXTERIOR | 1680 | 0.2    | 55             | 64.7              | 180               | 150        | 4.4    | 5.0         | 2    | 8        | 24           | 18           | CV 5.4        | 55               | 1                      |         |    |
| RC 2614      | TSI                      | TISSUE 2614            | 750  | 0.2    | 55             | 20.7              | 180               | 150        | 1.4    | 5.0         | 2    | 8        | 15           | 15           | CV 5.2        | 40               | 0.75                   |         |    |
| RC 2615      | TSI                      | FUME HOOD 2615         | 200  | 0.2    | 55             | 5.5               | 180               | 150        | 0.4    | 5.0         | 2    | 8        | 9            | 6            | CV 5.1        | 10               | 0.75                   |         |    |
| RC 2616      | TSI                      | TISSUE 2616            | 600  | 0.2    | 55             | 16.5              | 180               | 150        | 1.1    | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |    |

| REHEAT COILS |                          |                                       |            |        |                |                   |                   |            |            |             |      |          |              |              |               |                  |                        |         |
|--------------|--------------------------|---------------------------------------|------------|--------|----------------|-------------------|-------------------|------------|------------|-------------|------|----------|--------------|--------------|---------------|------------------|------------------------|---------|
| UNIT NO.     | MANUFACTURER & MODEL NO. | SERVICE                               | CFM        | A.P.D. | ENT. AIR (°F.) | CAPACITY (M.B.H.) | HEATING HOT WATER |            |            |             | ROWS | FINS/IN. | LENGTH (IN.) | HEIGHT (IN.) | CONTROL VALVE | OPER. WT. (LBS.) | BRANCH PIPE SIZE (IN.) | REMARKS |
|              |                          |                                       |            |        |                |                   | ENT. (°F.)        | LVG. (°F.) | G.P.M.     | P. D. (FT.) |      |          |              |              |               |                  |                        |         |
| RC B101      | TSI                      | P B101                                | 250        | 0.2    | 55             | 6.9               | 180               | 150        | 0.5        | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |
| RC B102      | TSI                      | P B102                                | 575        | 0.2    | 55             | 15.9              | 180               | 150        | 1.1        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B103      | TSI                      | P B103                                | 475        | 0.2    | 55             | 13.1              | 180               | 150        | 0.9        | 5.0         | 2    | 8        | 12           | 12           | CV 5.1        | 20               | 0.75                   |         |
| RC B104      | TSI                      | P B104                                | 250        | 0.2    | 55             | 6.9               | 180               | 150        | 0.5        | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |
| RC B111      | TSI                      | P B111                                | 250        | 0.2    | 55             | 6.9               | 180               | 150        | 0.5        | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |
| RC B112      | TSI                      | P B112                                | 575        | 0.2    | 55             | 15.9              | 180               | 150        | 1.1        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B113      | TSI                      | P B113                                | 475        | 0.2    | 55             | 13.1              | 180               | 150        | 0.9        | 5.0         | 2    | 8        | 12           | 12           | CV 5.1        | 20               | 0.75                   |         |
| RC B114      | TSI                      | P B114                                | 250        | 0.2    | 55             | 6.9               | 180               | 150        | 0.5        | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |
| RC B115A     | TSI                      | I B115A                               | 120        | 0.2    | 55             | 3.3               | 180               | 150        | 0.3        | 5.0         | 2    | 8        | 6            | 6            | CV 5.1        | 5                | 0.75                   |         |
| RC B115B     | TSI                      | I B115B                               | 50         | 0.2    | 55             | 1.4               | 180               | 150        | 0.1        | 5.0         | 2    | 8        | 6            | 6            | CV 5.1        | 5                | 0.75                   | RF 22   |
| RC B115C     | TSI                      | I B115C                               | 50         | 0.2    | 55             | 1.4               | 180               | 150        | 0.1        | 5.0         | 2    | 8        | 6            | 6            | CV 5.1        | 5                | 0.75                   |         |
| RC B115D     | TSI                      | I B115D                               | 50         | 0.2    | 55             | 1.4               | 180               | 150        | 0.1        | 5.0         | 2    | 8        | 6            | 6            | CV 5.1        | 5                | 0.75                   |         |
| RC B116      | TSI                      | H B116                                | 240        | 0.2    | 55             | 6.8               | 180               | 150        | 0.5        | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |
| RC B117      | TSI                      | H B117                                | 270        | 0.2    | 55             | 7.5               | 180               | 150        | 0.5        | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |
| RC B118      | TSI                      | ANIMAL HOLDING B118                   | 190        | 0.2    | 55             | 5.2               | 180               | 150        | 0.3        | 5.0         | 2    | 8        | 9            | 6            | CV 5.1        | 10               | 0.75                   |         |
| RC B119      | TSI                      | ANIMAL HOLDING B119                   | 190        | 0.2    | 55             | 5.2               | 180               | 150        | 0.3        | 5.0         | 2    | 8        | 9            | 6            | CV 5.1        | 10               | 0.75                   | 32      |
| RC B120      | TSI                      | CORR. B120                            | 450        | 0.2    | 55             | 12.4              | 180               | 150        | 0.8        | 5.0         | 2    | 8        | 12           | 12           | CV 5.1        | 20               | 0.75                   |         |
| RC B121      | TSI                      | ULTRA SOUND B121                      | 630        | 0.2    | 55             | 17.3              | 180               | 150        | 1.2        | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   | 3       |
| RC B122      | TSI                      | OPTICAL B122                          | 350        | 0.2    | 55             | 9.6               | 180               | 150        | 0.6        | 5.0         | 2    | 8        | 12           | 9            | CV 5.1        | 15               | 0.75                   |         |
| RC B303      | TSI                      | CORRIDOR B302, B303                   | 1465       | 0.2    | 55             | 40.3              | 180               | 150        | 2.7        | 5.0         | 2    | 8        | 24           | 15           | CV 5.2        | 45               | 0.75                   |         |
| RC B307      | TSI                      | CORRIDOR B306, B307                   | 1755       | 0.2    | 55             | 48.3              | 180               | 150        | 3.3        | 5.0         | 2    | 8        | 24           | 18           | CV 5.3        | 55               | 0.75                   |         |
| RC B501      | TSI                      | H B501, P B501A                       | 860        | 0.2    | 55             | 23.7              | 180               | 150        | 1.6        | 5.0         | 2    | 8        | 18           | 12           | CV 5.2        | 30               | 0.75                   |         |
| RC B502      | TSI                      | H B502, P B502A                       | 605        | 0.2    | 55             | 16.7              | 180               | 150        | 1.2        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B503      | TSI                      | H B503, P B503A                       | 860        | 0.2    | 55             | 23.7              | 180               | 150        | 1.6        | 5.0         | 2    | 8        | 18           | 12           | CV 5.2        | 30               | 0.75                   |         |
| RC B504      | TSI                      | H B504, P B504A                       | 605        | 0.2    | 55             | 16.7              | 180               | 150        | 1.2        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B505      | TSI                      | H B505, P B505A                       | 860        | 0.2    | 55             | 23.7              | 180               | 150        | 1.6        | 5.0         | 2    | 8        | 18           | 12           | CV 5.2        | 30               | 0.75                   |         |
| RC B506      | TSI                      | H B506, P B506A                       | 605        | 0.2    | 55             | 16.7              | 180               | 150        | 1.2        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B507      | TSI                      | H B507, P B507A, P B507B              | 1220       | 0.2    | 55             | 33.6              | 180               | 150        | 2.3        | 5.0         | 2    | 8        | 24           | 12           | CV 5.2        | 40               | 0.75                   |         |
| RC B508      | TSI                      | H B508, P B508A                       | 860        | 0.2    | 55             | 23.7              | 180               | 150        | 1.6        | 5.0         | 2    | 8        | 18           | 12           | CV 5.2        | 30               | 0.75                   |         |
| RC B509      | TSI                      | H B509, P B509A                       | 605        | 0.2    | 55             | 16.7              | 180               | 150        | 1.2        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B511      | TSI                      | H B511, P B511A, P B511B              | 1170       | 0.2    | 55             | 32.2              | 180               | 150        | 2.2        | 5.0         | 2    | 8        | 24           | 12           | CV 5.2        | 40               | 0.75                   |         |
| RC B512      | TSI                      | DIRTY CAGE B512                       | 540        | 0.2    | 55             | 14.9              | 180               | 150        | 1          | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B513      | TSI                      | CARCASS B513                          | 870        | 0.2    | 55             | 24                | 180               | 150        | 1.6        | 5.0         | 2    | 8        | 18           | 12           | CV 5.2        | 30               | 0.75                   |         |
| RC B514      | TSI                      | BREAKROOM B514                        | 285        | 0.2    | 55             | 7.9               | 180               | 150        | 0.6        | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   |         |
| RC B506      | TSI                      | GOWNING B506                          | 145        | 0.2    | 55             | 4                 | 180               | 150        | 0.3        | 5.0         | 2    | 8        | 6            | 6            | CV 5.1        | 5                | 0.75                   |         |
| RC B701      | TSI                      | H B701, P B701A                       | 605        | 0.2    | 55             | 16.7              | 180               | 150        | 1.2        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B702      | TSI                      | H B702, P B702A                       | 860        | 0.2    | 55             | 23.7              | 180               | 150        | 1.6        | 5.0         | 2    | 8        | 18           | 12           | CV 5.2        | 30               | 0.75                   |         |
| RC B703      | TSI                      | H B703, P B703A                       | 605        | 0.2    | 55             | 16.7              | 180               | 150        | 1.2        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B704      | TSI                      | H B704, P B704A                       | 860        | 0.2    | 55             | 23.7              | 180               | 150        | 1.6        | 5.0         | 2    | 8        | 18           | 12           | CV 5.2        | 30               | 0.75                   |         |
| RC B705      | TSI                      | H B705, P B705A                       | 605        | 0.2    | 55             | 16.7              | 180               | 150        | 1.2        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B706      | TSI                      | H B706, P B706A                       | 860        | 0.2    | 55             | 23.7              | 180               | 150        | 1.6        | 5.0         | 2    | 8        | 18           | 12           | CV 5.2        | 30               | 0.75                   |         |
| RC B707      | TSI                      | H B707, P B707A, P B707B              | 1220       | 0.2    | 55             | 33.6              | 180               | 150        | 2.3        | 5.0         | 2    | 8        | 24           | 12           | CV 5.2        | 40               | 0.75                   |         |
| RC B708      | TSI                      | H B708, P B708A                       | 605        | 0.2    | 55             | 16.7              | 180               | 150        | 1.2        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B709      | TSI                      | H B709, P B709A                       | 860        | 0.2    | 55             | 23.7              | 180               | 150        | 1.6        | 5.0         | 2    | 8        | 18           | 12           | CV 5.2        | 30               | 0.75                   |         |
| RC B711      | TSI                      | H B711, P B711A, P B711B              | 1170       | 0.2    | 55             | 32.2              | 180               | 150        | 2.2        | 5.0         | 2    | 8        | 24           | 12           | CV 5.2        | 40               | 0.75                   |         |
| RC B712      | TSI                      | STERILE CAGE WASH B712                | 665        | 0.2    | 55             | 18.3              | 180               | 150        | 1.3        | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |
| RC B713      | TSI                      | CLEAN CAGE B713                       | 585        | 0.2    | 55             | 15.6              | 180               | 150        | 1.1        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B714      | TSI                      | IRRADIATOR B714                       | 300 RF 363 | 0.2    | 55             | 8.3 RF 86         | 180               | 150        | 0.6 RF 363 | 5.0         | 2    | 8        | 12 RF 363    | 6            | CV 5.1        | 10 RF 363        | 0.75                   |         |
| RC B715      | TSI                      | VEST B715, FEED B718                  | 665        | 0.2    | 55             | 18.3              | 180               | 150        | 1.3        | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |
| RC B716      | TSI                      | ANIMAL RECEIVING B716                 | 600        | 0.2    | 55             | 16.7              | 180               | 150        | 1.2        | 5.0         | 2    | 8        | 12           | 12           | CV 5.2        | 20               | 0.75                   |         |
| RC B717      | TSI                      | QUARANTINE B717                       | 310        | 0.2    | 55             | 8.6               | 180               | 150        | 0.6        | 5.0         | 2    | 8        | 9            | 9            | CV 5.1        | 10               | 0.75                   |         |
| RC B902      | TSI                      | BASEMENT OFFICE AREA                  | 745        | 0.2    | 55             | 20.5              | 180               | 150        | 1.4        | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |
| RC B905      | TSI                      | RESTROOMS B903, B905                  | 1000       | 0.2    | 55             | 27.5              | 180               | 150        | 1.9        | 5.0         | 2    | 8        | 18           | 15           | CV 5.2        | 35               | 0.75                   |         |
| RC B010      | TSI                      | ENTRY B010, AIRLOCK B016, OFFICE B017 | 1500       | 0.2    | 55             | 41.3              | 180               | 150        | 2.8        | 5.0         | 2    | 8        | 18           | 18           | CV 5.3        | 55               | 0.75                   | 32      |
| RC B011      | TSI                      | IMAGING EQUIP. B011                   | 1200       | 0.2    | 55             | 28.4              | 180               | 150        | 1.8        | 5.0         | 2    | 8        | 18           | 18           | CV 5.2        | 40               | 0.75                   |         |
| RC B012      | TSI                      | MICRO SPECT/CT B012                   | 470        | 0.2    | 55             | 12.9              | 180               | 150        | 0.9        | 5.0         | 2    | 8        | 6            | 12           | CV 5.1        | 20               | 0.75                   |         |
| RC B013      | TSI                      | MICRO PET/CT B012                     | 480        | 0.2    | 55             | 13.5              | 180               | 150        | 0.9        | 5.0         | 2    | 8        | 6            | 12           | CV 5.1        | 20               | 0.75                   |         |
| RC B014      | TSI                      | PROCEDURE B014                        | 640        | 0.2    | 55             | 17.6              | 180               | 150        | 1.2        | 5.0         | 2    | 8        | 15           | 12           | CV 5.2        | 25               | 0.75                   |         |
| RC B015      | TSI                      | HOT CELL LAB B015                     | 1900       | 0.2    | 55             | 52.3              | 180               | 150        | 3.5        | 5.0         | 2    | 8        | 30           | 18           | CV 5.3        | 70               | 1                      |         |
| RC B017      | TSI                      | MRI CONTROL B017                      | 450        | 0.2    | 55             | 12.4              | 180               | 150        | 0.9        | 5.0         | 2    | 8        | 12           | 9            | CV 5.1        | 15               | 0.75                   |         |
| RC B018      | TSI                      | MRI PROC. B018                        | 475        | 0.2    | 55             | 13.1              | 180               | 150        | 0.9        | 5.0         | 2    | 8        | 12           | 9            | CV 5.1        | 15               | 0.75                   |         |
| RC B019      | TSI                      | ANIMAL HOLDING B019                   | 260        | 0.2    | 55             | 7.2               | 180               | 150        | 0.5        | 5.0         | 2    | 8        | 12           | 6            | CV 5.1        | 10               | 0.75                   | 32      |
| RC B021      | TSI                      | MRI B021, B022                        | 2510       | 0.2    | 55             | 69.1              | 180               | 150        | 4.7        | 5.0         | 2    | 8        | 36           | 18           | CV 5.4        | 80               | 1                      |         |
| RC B023      | TSI                      | TEM B023                              | 320        | 0.2    | 55             | 8.8               | 180               | 150        | 0.6        | 5.0         | 2    | 8        | 9            | 9            | CV 5.1        | 10               | 0.75                   |         |
| RC B025      | TSI                      | MICROSCOPE AREA                       | 1025       | 0.2    | 55             | 34.6              | 180               | 150        | 2.4        | 5.0         | 2    | 8        | 24           | 15           | CV 5.2        | 45               | 0.75                   |         |